

16 x 29mm FL, Grade 1, Double-Convex Lens



Stock **#74-131** CLEARANCE **15 In Stock**

-

1

+

C\$14^{.35}

ADD TO CART

Volume Pricing	
Qty 1+	C\$14.35 each
Need More?	Request Quote

Product Downloads

General

Type:

Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

16.00

Optical Properties

Effective Focal Length EFL (mm):

29.00

Coating:

Anti-Reflection Coating	
1.81	f/#:
0.28	Numerical Aperture NA:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
 - Quantities Extremely Limited, Buy While Supplies Last
 - For Even Mbre Deals, Check out [Mega Clearance: Optics](#)
- Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

15 - 19.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

