


1.65μm, 25mm Diameter, Infrared Longpass Filter



Infrared (IR) Longpass Filters

Stock **#68-652** ☐ In Stock



1



C\$449.40

ADD TO CART

Qty 1-9

C\$449.40

Qty 10+

C\$403.62

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Optical Density OD (Average):
≥3.0

Cut-On Wavelength (nm):
1,650.00

Substrate: ☐

Silicon (Si)
Operating Temperature (°C): -62 to +71
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >85
Transmission Wavelength (nm): 1730 - 3300
Transmission Wavelength (µm): 1.73 - 3.30
Type: Longpass Filter
Blocking Wavelength Range (nm): 200 - 1650
Parallelism (arcmin): <10
Clear Aperture (%): 90
Slope Factor (%): <7
Cut-On Wavelength (µm): 1.65 ±0.07
Note: Transmission at cut-on wavelength is 5% of peak transmission.
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant