

## 17.5 x 16mm FL, Grade 1, Double-Convex Lens



Stock #73-860 CLEARANCE **5 In Stock**

C\$14<sup>.35</sup>

ADD TO CART

Volume Pricing	
Qty 1+	C\$14.35 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Double-Convex Lens Type:

#### Physical & Mechanical Properties

17.50 Diameter (mm):

#### Optical Properties

16.00 Effective Focal Length EFL (mm):

f#:

0.91

Numerical Aperture NA:

0.55

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

15 - 19.9mm Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

**Note:** Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

## Technical Information

