

**TECHSPEC® 16mm, f/2.8 Ci Series Fixed Focal Length Lens**



16mm Focal Length

Stock **#85-350** **11 In Stock**

- 1 + C\$491<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-24	C\$491.40 each
Qty 25+	C\$442.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Ci Series **Product Family:**  
Fixed Focal Length Lens **Type:**

**Physical & Mechanical Properties**

Fixed **Iris Option:**  
Length (mm):

40.80

Maximum Diameter (mm):

26.5

Outer Diameter (mm):

26.5

Weight (g):

37

Maximum Rear Protrusion (mm):

1.09

Diameter (mm):

26.50

## Optical Properties

Horizontal Field of View @ Max Sensor Format:

61.4mm - 30.9°

Field of View at Max Sensor Format:

Horizontal: 59.7mm - 30.9°

Vertical: 44.6mm - 23.4°

Diagonal: 75mm - 38.2°

Horizontal Field of View, 2/3" Sensor:

61.4mm - 30.9°

Horizontal Field of View, 1/1.8" Sensor:

50.1mm - 25.2°

Horizontal Field of View, 1/2" Sensor:

44.5mm - 22.7°

Horizontal Field of View, 1/2.5" Sensor:

39.6mm - 20.2°

Horizontal Field of View, 1/3" Sensor:

33.3mm - 17.1°

Horizontal Field of View, 1/4" Sensor:

25mm - 12.8°

Maximum Image Circle (mm):

11.00

Numerical Aperture NA, Object Side:

0.0235

Number of Elements (Groups):

7 (6)

Focal Length FL (mm):

16.00

Working Distance (mm):

100 - ∞

Aperture (f#):

f/2.8

Coating:

425 - 675nm BBAR

Coating Specification:

425 - 675nm BBAR

Entrance Pupil Position (mm):

19.19

Object Space Principal Plane (mm):

21.30

Image Space Principal Plane (mm):

-3.00

Maximum Distortion (%):

-0.77

Exit Pupil Position (mm):

-5.43

Lens Wavelength Range:

VIS

## Sensor

Maximum Sensor Format:

2/3"

Pixel Size (μm):

2.74

## Threading & Mounting

Filter Thread:

M25.5 x 0.50 (Male)

Filter Thread Adapter:

[#89-941 \(Required\)](#)

Front Thread:

M22.0 x 0.75 (Male)

Mount:

## Environmental & Durability Factors

**Storage Temperature (°C):**  
-20 to +60

**Type of Ruggedization:**  
Industrial (Fixed Aperture with Simplified Mechanics)

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
View

**Reach 235:**  
Compliant

## Product Details

These compact lenses are designed specifically for volume integration into applications such as analytical medical devices, including benchtop-based blood analyzers. For customized  $f/\#$  versions to best suit your instrumentation application needs and to discuss volume requirements, please [contact us](#).


- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8 $\mu$ m Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- **Ruggedized (Cr) Designs** Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a **VIS-NIR Broadband Anti-Reflection (BBAR) Coating**.
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC **Ingress Protection** Code IPX7 and IPX9K.


## Technical Information




#85-350, 16mm,  $f/2.8$  Ci Series Fixed Focal Length Lens, Distortion Plot




#85-350, 16mm,  $f/2.8$  Ci Series Fixed Focal Length Lens, Relative Illumination Plot




#85-350, 16mm, f/2.8 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#85-350, 16mm, f/2.8 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f2.8



#85-350, 16mm, f/2.8 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f2.8



#85-350, 16mm, f/2.8 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f2.8



#85-350, 16mm, f/2.8 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f2.8

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm
50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm

## Compatible Cameras

---