

[See all 10 Products in Family](#)

# 1.7mm FL, f/5.6, Low Distortion M12 Lens



1.7mm FL, Low Distortion M12 Lens

Stock **#75-196** NEW **1 In Stock**

-

1

+

C\$1,204<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$1,204.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                        |
|----------------------------------|------------------------|
| M12 Imaging Lens                 | Imaging Lens Type:     |
| Physical & Mechanical Properties |                        |
| Fixed                            | Iris Option:           |
| 32.83                            | Length (mm):           |
| 26.5                             | Maximum Diameter (mm): |

|       |                      |
|-------|----------------------|
| 26.5  | Outer Diameter (mm): |
| 12    | Weight (g):          |
| 32.83 | Maximum Length (mm): |

Optical Properties

|                                                           |                                               |
|-----------------------------------------------------------|-----------------------------------------------|
| 109.1°                                                    | Horizontal Field of View @ Max Sensor Format: |
| Horizontal: 109.1°<br>Vertical: 93.0°<br>Diagonal: 120.7° | Field of View at Max Sensor Format:           |
| 1.70                                                      | Focal Length FL (mm):                         |
| 100 - ∞                                                   | Working Distance (mm):                        |
| f/5.6                                                     | Aperture (f/#):                               |
| -0.32                                                     | Maximum Distortion (%):                       |
| 34.8                                                      | Exit Pupil Position (mm):                     |
| VIS                                                       | Lens Wavelength Range:                        |

Sensor

|        |                          |
|--------|--------------------------|
| 1/2.5" | Optimized Sensor Format: |
| 1/2.5" | Maximum Sensor Format:   |

Threading & Mounting

|                    |        |
|--------------------|--------|
| S-Mount (M12 x0.5) | Mount: |
|--------------------|--------|

Environmental & Durability Factors

|            |                           |
|------------|---------------------------|
| -20 to +60 | Storage Temperature (°C): |
|------------|---------------------------|

Regulatory Compliance


|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

Product Details


- Distortion as low as -0.02%
- Up to 1/1.8", S-Mount Options
- 1.7mm - 5mm Focal Lengths

Ultra Low Distortion Wide Angle Lenses are designed to achieve less than -0.02% distortion over a 76.9° field of view, less than -0.32% distortion over a 109.1° field of view, or less than -0.51% distortion over a 59.8° field of view. The ultra-low distortion values of these lenses ensure imaging with straight lines and natural object shapes, helping to reduce post-processing requirements. These lenses offer high transmission from the VIS to NIR and are available in focal lengths of 1.70, 3.00, and 5.00mm. Ultra Low Distortion Wide Angle Lenses' low focal lengths allow for capturing more of the scene in a single frame. These lenses are ideal for surveillance, security, robotics, drive assistance systems, and [factory automation applications](#).


Technical Information




1.7mm FL, f/5.6, Low Distortion M12 Lens, Distribution Plot



1.7mm FL, f/5.6, Low Distortion M12 Lens, MTF Plot



1.7mm FL, f/5.6, Low Distortion M12 Lens, Relative Illumination Plot



1.7mm FL, f/5.6, Low Distortion M12 Lens, Transmission Plot