

TECHSPEC®

18.0mm Dia. x 22.5mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#49-890** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$50.40

ADD TO CART

Qty 1-9
C\$50.40
Qty 10+
C\$45.50
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):
22.50 @ 587.6nm

Back Focal Length BFL (mm): 20.26
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 1.53
Radius R₁ (mm): 17.66
Clear Aperture CA (mm): 17
f/#: 1.25
Numerical Aperture NA: 0.40
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View