

TECHSPEC®

18mm Dia. x 18mm FL, YAG-BBAR Coated, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-254** ☐ In Stock

☐ [Other Coating Options](#)

1

C\$65.80

ADD TO CART

Qty 1-9

C\$65.80

Qty 10+

C\$59.15

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Back Focal Length BFL (mm):

16.69
Effective Focal Length EFL (mm): 18.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.44
Radius R₁=R₂ (mm): 27.22
Clear Aperture CA (mm): 17.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 2500
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant