

TECHSPEC® 18mm Dia. x 60mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-709** ☐ In Stock
[Other Coating Options](#)

1 **C\$137.20**

ADD TO CART

Qty 1-5
C\$137.20
Qty 6+
C\$109.90
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 56.79
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 17.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.85 ±0.20
Center Thickness CT 1 (mm) : 3.85 ±0.10
Center Thickness CT 2 (mm) : 2.00 ±0.10
Radius R₁ (mm) : 42.51
Radius R₂ (mm) : -26.24
Radius R₃ (mm) : -226.77
Edge Thickness ET (mm) : 4.71
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 3.33
Numerical Aperture NA : 0.15
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View