

TECHSPEC® 18mm Dia. x 35mm FL, YAG-BBAR Coated, Achromatic Doublet Lens



YAG-BBAR Coated Achromatic Lenses



Stock **#15-477** ☐ In Stock

☐ [Other Coating Options](#)

1

C\$135.80

ADD TO CART

Qty 1-5

C\$135.80

Qty 6+

C\$108.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):

35.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 30.72
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 17.00
Centering (arcmin): <1
Center Thickness CT (mm): 7.61 ±0.20
Center Thickness CT 1 (mm): 6.01 ±0.10
Center Thickness CT 2 (mm): 1.60 ±0.10
Radius R ₁ (mm): 24.26
Radius R ₂ (mm): -16.23
Radius R ₃ (mm): -152.99
Edge Thickness ET (mm): 5.61
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.94
Numerical Aperture NA: 0.26
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 500 - 1100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View