

TECHSPEC® 1" Dia, 1" FL UV Enhanced Alum., Spherical Mirror



Stock **#43-535** [CONTACT US](#)

- 1 + **C\$161.00**

ADD TO CART

Qty 1-9
C\$161.00
Qty 10+
C\$136.50
Volume Pricing
Request Quote

Get Product Downloads



Substrate:  **BOROFLOAT®**

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

M4
Diameter (inches): 1.0
Diameter (mm): 25.40 +0/-0.3
Diameter Tolerance (inches): +0/-0.01
Effective Focal Length EFL (inches): 1.00
Effective Focal Length EFL (mm): 25.40
Radius of Curvature (mm): 50.80
Aperture (f/#): f/1
Coating: Enhanced Aluminum (250-700nm)
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating Type: Metal
Back Surface: Ground
Edge Thickness ET (inches): 0.25
Edge Thickness ET (mm): 6.35
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: 0.5 J/cm ² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant