

[See all 13 Products in Family](#)

1X Objective, CFI Plan Achromatic UW

See More by [Nikon](#)



Stock #75-349 NEW 2 In Stock

⊖ 1 ⊕ C\$2,702⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,702.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
MRL00012

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Type:
Microscope Objective

Style:
Infinity Corrected

Manufacturer:
Nikon

Physical & Mechanical Properties

25 **Field of View (mm):**

56.70 **Length excluding Threads (mm):**

31 **Maximum Diameter (mm):**

190 **Weight (g):**

Optical Properties

N/A **Compatible Cover Glass Thickness (mm):**

6.4 **Horizontal Field of View, 1/2" Sensor:**

8.8 **Horizontal Field of View, 2/3" Sensor:**

1X **Magnification:**

0.04 **Numerical Aperture NA:**

3.2 **Working Distance (mm):**

25 **Field Number (mm):**

59.9 **Parfocal Length (mm):**

N/A **Immersion Liquid:**

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

M25 x 0.75 **Mounting Threads:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1X to 100X)

Nikon's CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capability for demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1X up to 100X magnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.

Technical Information

