

[See all 72 Products in Family](#)

TECHSPEC® 200 x 200mm Linear Polarizing Film (XP42-40)



Stock **#29-496** **9 In Stock**

C\$163^{.80}

ADD TO CART

Volume Pricing	
Qty 1-10	C\$163.80 each
Qty 11-25	C\$145.18 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Polarization axis is parallel to marking on protective film. **Note:**

Physical & Mechanical Properties

200.0 x 200.0 ±1.0 **Dimensions (mm):**

Thickness (mm):

0.40 ±0.05

Polarizing Film

Construction:

Optical Properties

Coating:
Uncoated, Protective Film on Both Sides

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate:
[Polymer Film XP42-40](#)

Transmission (%):
Single: 42 ±2
Parallel: 36.4
Crossed: <0.004 (nominal at 555nm)

Wavelength Range (nm):
400 - 700

Polarization Efficiency (%):
>99.98 (nominal at 555nm)

Transmission, Single (%):
42 ±2

Transmission, Parallel (%):
36.4

Transmission, Crossed (%):
<0.004 (nominal at 555nm)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information



XP44 - Linear Polarizer

