

[See all 12 Products in Family](#)

TECHSPEC® 20.0mm Dia x 3mm Thick 635-670/1064nm, Zerodur Dual Band Laser Mirror



Stock **#29-064** **9 In Stock**

- 1 + C\$268.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$268.80 each
Qty 6-25	C\$215.60 each
Qty 26-49	C\$201.60 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

3.00 ±0.20 **Thickness (mm):**

20.00 +0.00/-0.20 **Diameter (mm):**

90	Clear Aperture (%) :
30	Parallelism (arcsec) :
Commercial Polish	Back Surface :
Protective as needed	Bevel :
Ground	Edges :

Optical Properties

ZERODUR®	Substrate : <input type="checkbox"/>
20-10	Surface Quality :
Laser Mirror (635, 670, 1064nm)	Coating :
635, 670, 1064	Design Wavelength DWL (nm) :
Rabs >99.5% @ 635, 670 & 1064nm	Coating Specification :
Dielectric	Coating Type :
20 J/cm2 @ 1064nm	Damage Threshold, By Design : <input type="checkbox"/>

Regulatory Compliance

View	Certificate of Conformance :
----------------------	-------------------------------------

Product Details

- >99.5% Reflectivity at Design Wavelengths
- Low Coefficient of Thermal Expansion
- 532/1064nm or 635/670/1064nm Wavelength Bands

TECHSPEC® Zerodur® Dual Band Laser Line Mirrors feature high reflectivity coatings with either two or three wavelength bands on a durable Zerodur® substrates. The ZERODUR® substrates have a low coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® Zerodur® Dual Band Laser Line Mirrors are available in a highly reflective 532/1064nm or 635/670/1064nm dual band coatings and multiple standard diameter options for Nd:YAG lasers and red and green guide beams. These mirrors are ideal for beam steering applications in both laboratory and OEM laser systems.