


TECHSPEC® 20mm Diameter x -100 FL, VIS-NIR Coated, Plano-Concave Lens



TECHSPEC VIS-NIR Coated Plano-Concave (PCV) Lenses



Stock **#22-246** ☐ In Stock

☐ [Other Coating Options](#)

1

C\$65.80

ADD TO CART

Qty 1-9

C\$65.80

Qty 10+

C\$59.15

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-100.00
Substrate: N-BK7
f#: 4.00
Numerical Aperture NA: 0.13
Coating: VIS-NIR (400-1000nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -102.88
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 19.00
Coating Specification: R_{abs} ≤0.25% @ 880nm R_{avg} ≤1.25% @ 400 - 870nm R_{avg} ≤1.25% @ 890 - 1000nm
Edge Thickness ET (mm): 4.42
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -51.68
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant