

TECHSPEC® 20.0mm Dia. x 40.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#47-886** ☐ In Stock
[Other Coating Options](#)

1 **C\$58.10**

ADD TO CART

Qty 1-9
C\$58.10
Qty 10+
C\$52.15
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Back Focal Length BFL (mm): 36.77
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.90 ±0.10
Edge Thickness ET (mm): 2.32
Radius R₁ (mm): 20.67
Clear Aperture CA (mm): 19
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant