

TECHSPEC® 20.0mm Dia. x 50.0mm FL, YAG-BBAR Coated Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock #88-873 In Stock

[Other Coating Options](#)

⊖ 1 ⊕ **C\$63.00**

ADD TO CART

Qty 1-9

C\$63.00

Qty 10+

C\$56.70

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Back Focal Length BFL (mm):
47.87

Coating:
YAG-BBAR (500-1100nm)

Coating Specification:
R_{abs} <0.25% @ 532nm
R_{abs} <0.25% @ 1064nm
R_{avg} <1.0% @ 500 - 1100nm

Substrate:
[N-BK7](#)

Surface Quality:
40-20

Power (P-V) @ 632.8nm:
1.5λ

Irregularity (P-V) @ 632.8nm:
λ/4

Focal Length Tolerance (%):
±1

Centering (arcmin):
<1

Center Thickness CT (mm):
3.23 ±0.10

Edge Thickness ET (mm):
1.22

Radius R₁ (mm):
25.84

Clear Aperture CA (mm):
19

f#:
2.5

Numerical Aperture NA:
0.20

Type:
Plano-Convex Lens

Bevel:
Protective bevel as needed

Wavelength Range (nm):
500 - 1100

Damage Threshold, By Design:
5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)