

200µm 0.22 NA VIS/NIR Fiber, 25m Length



Stock **#57-092** ☐ In Stock

-

1

+

C\$292.60

ADD TO CART

Qty 1-4
C\$292.60
Qty 5+
C\$257.60
Volume Pricing
Request Quote

Get Product Downloads

Acceptance Angle (°):
25.4

Buffer Material:
Polyimide

Cladding Diameter (µm):
220 ±4

Coating: VS/NIR
Minimum Bend Radius (mm): 44/22 (Continuous/Momentary)
Substrate: Fused Silica (Corning 7980)
Length (m): 25.00
Numerical Aperture NA: 0.22
Operating Temperature (°C): -190 to +390
Outer Diameter (µm): 239 ±5
Core Diameter (µm): 200 ±4
Index of Refraction n_d - Core: 1.457
Index of Refraction n_d - Cladding: 1.440
Wavelength Range (nm): 300 - 2400
Numerical Aperture (NA) Tolerance: ±0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View