

[See all 15 Products in Family](#)

## 200mW, 589nm LC Turnkey Laser Fiber SMA



Low Cost Turnkey Laser & Power Supply (Included)



Stock **#19-506** **2 In Stock**

⊖ 1 ⊕ C\$18,200<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	C\$18,200.00 each
Qty 5+	C\$16,380.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads



### General

Warm-Up Time (minutes):  
<10

Type of Laser:  
Diode

Laser Class - CDRH:  
IIIb

10000 Mean Time to Failure MTF (hours):

## Physical & Mechanical Properties

142.5 x 60 x 50 Dimensions (mm):

27.4 Beam Height from Base Plate (mm):

## Optical Properties

589.00 Wavelength (nm):

±2 Wavelength Tolerance (nm):

Yellow Color:

0.22 Fiber Numerical Aperture NA (1/e<sup>2</sup>):

## Electrical

200 Output Power (mW):

<2% RMS over 4 hours Power Stability (%):

1 Modulation Frequency (kHz):

## Hardware & Interface Connectivity

88 x 145 x 83 Power Supply:

90-264VAC Power Requirement:

Fiber-Coupled Output Type:

SMA Connector:

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

## Product Details

- Multiple Colors and Wavelengths Available
- Ideal for Microscopy Applications
- TE Cooled

Low Cost Turnkey Lasers offer excellent beam quality and output powers up to 50mW. These lasers feature compact designs for simplified integration and manually adjustable output power through the control box. Each laser features TE cooling and flexible interface allowing for digital or analog modulation, with multiple color and wavelength options available. Low Cost Turnkey Lasers are ideal for research, flow cytometry, and microscope illumination applications.

**Note:** Power supply included. Fiber-coupled lasers include 1m SMA905 coupled fiber.

## Technical Information

