

TECHSPEC® 20.0mm Diameter x -50 FL, NIR I Coated, Plano-Concave Lens



Stock **#49-533** ☐ In Stock
[Other Coating Options](#)

1 **C\$60.90**

ADD TO CART

Qty 1-9
C\$60.90
Qty 10+
C\$54.95
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-50.00

Substrate: N-BK7
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: NIR I (600-1050nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): -52.31
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 19.00
Coating Specification: R_{avg} ≤0.5% @ 600 - 1050nm
Edge Thickness ET (mm): 5.21
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -25.84
Surface Quality: 40-20
Damage Threshold, By Design: 7 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant