

200μm 0.22 NA VIS/NIR Fiber, 25m Length



Stock **#57-092** [CONTACT US](#)

-

1

+

C\$298²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$298.20 each
Qty 5-24	C\$263.20 each
Need More?	Request Quote

Product Downloads

General	
	Note: Fiber ends are not polished.
Physical & Mechanical Properties	
	Cladding Diameter (μm): 220 ±4
	Minimum Bend Radius (mm): 44/22 (Continuous/Momentary)

25.00	Length (m):
239 ±5	Outer Diameter (µm):
200 ±4	Core Diameter (µm):
Optical Properties	
25.4	Acceptance Angle (°):
VIS/NIR	Coating:
Fused Silica	Substrate: □
0.22	Numerical Aperture NA:
1.457	Index of Refraction (n _d) - Core:
1.440	Index of Refraction (n _d) - Cladding:
300 - 2400	Wavelength Range (nm):
±0.02	Numerical Aperture (NA) Tolerance:
Material Properties	
Polyimide	Buffer Material:
Environmental & Durability Factors	
-190 to +390	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

UV/VIS Optical Fibers

- High OH Content
- Fused Silica Core
- Stepped Index
- Multimode Fiber

VIS/NIR Optical Fibers

- Low OH Content
- Ideal for Use with NIR Diode Lasers
- Fused Silica Core
- Stepped Multimode Fiber

Buffered Fiber Optics are ideal for regions of the UV/Visible and Visible/NIR spectrum not covered by our plastic optical fibers. These fibers have a fused silica core and cladding, as well as a polymer buffer for added protection. Fiber diameters of 50µm – 600µm feature a high temperature, high strength polyimide buffer, while the 1mm fibers are buffered with nylon for greater protection. Buffered Fiber Optics are offered in UV/MS or VIS/NIR Fibers in 10 and 25m lengths, from 50 to 600µm.

Note: Fiber ends are not polished.

Technical Information

