

TECHSPEC® 20mm Dia. x 80mm FL, NIR II Coated, Double-Convex Lens



Stock **#67-646** ☐ In Stock
[Other Coating Options](#)

1 **C\$61.60**

ADD TO CART

Qty 1-9
C\$61.60
Qty 10+
C\$55.30
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Back Focal Length BFL (mm):
78.67

Effective Focal Length EFL (mm): 80.00
Coating: NIR II (750-1550nm)
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.78
Radius R₁=R₂ (mm): 82.00
Clear Aperture CA (mm): 19.00
f#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant