

TECHSPEC®

20mm Dia. x 80mm FL, Uncoated, Double-Convex Lens



Stock **#63-554** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$44.10

ADD TO CART

Qty 1-9
C\$44.10
Qty 10+
C\$39.55
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Back Focal Length BFL (mm):
78.67

Effective Focal Length EFL (mm): 80.00
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.78
Radius R₁=R₂ (mm): 82.00
Clear Aperture CA (mm): 19.00
f#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant