

[See all 10 Products in Family](#)

20X Objective, Nikon CFI Super Fluor

See More by [Nikon](#)



Stock **#88-376** [CONTACT US](#)

- 1 + **C\$8,862⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	C\$8,862.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	MRF00201
Compatible Tube Lens Focal Length (mm):	Focal Length: 200mm
Type:	Microscope Objective
Style:	Infinity Corrected
Manufacturer:	Nikon
Physical & Mechanical Properties	
Field of View (mm):	1.10

58.90	Length (mm):
58.90	Length excluding Threads (mm):
33.5	Maximum Diameter (mm):
198.00	Weight (g):

Optical Properties	
0.17	Compatible Cover Glass Thickness (mm):
0.32mm	Horizontal Field of View, 1/2" Sensor:
0.44mm	Horizontal Field of View, 2/3" Sensor:
20X	Magnification:
0.75	Numerical Aperture NA:
1.0	Working Distance (mm):
22	Field Number (mm):
59.9	Parfocal Length (mm):
N/A	Immersion Liquid:

Sensor	
2/3"	Maximum Sensor Format:

Threading & Mounting	
M25 x0.75	Mounting Threads:


Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

• Superior UV Transmission
• High Numerical Aperture Designs
• Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



Dimensions (mm)						
Stock No.	Magnification	Parafoval Length	A	B	C	D
#88-374	4X	60.06	30.0	44.4	19.7	M25 x0
#88-375	10X	60.06	32.0	58.7	8.0	M25 x0
#88-376	20X	60.06	33.5	58.9	9.0	M25 x0
#88-377	40X	60.06	33.0	59.6	7.5	M25 x0