

## TECHSPEC® 22 x 22mm Protected Aluminum, λ/4 Mirror



Stock #33-510 [CONTACT US](#)

⊖ 1 ⊕ **C\$66.50**

**ADD TO CART**

Qty 1-5

C\$66.50

Qty 6+

C\$53.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):  
λ/4

Substrate:   
[BOROFLOAT®](#)

Back Surface:  
Ground

**Surface Quality:**

60-40

**Dimensions (mm):**

22.0 x 22.0

**Dimensional Tolerance (mm):**

+0/-0.5

**Coating Specification:**R<sub>avg</sub> >85% @ 400 - 700nmR<sub>avg</sub> >90% @ 400 - 2000nm**Coating:**

Protected Aluminum (400-2000nm)

**Coating Type:**

Metal

**Bevel:**

Protective bevel as needed

**Clear Aperture (%):**

85

**Edges:**

Fine Ground

**Thickness (mm):**

5.00 +0.5/-0

**Type:**

Flat Mirror

**Wavelength Range (µm):**

0.4 - 2.0

**Wavelength Range (nm):**

400 - 2000

**Length (mm):**

22.00

**Width (mm):**

22.00

**Damage Threshold, Reference:** 0.3 J/cm<sup>2</sup> @ 532nm & 1064nm, 10ns**Regulatory Compliance****RoHS 2015:**[Compliant](#)**Reach 224:**[Compliant](#)**Certificate of Conformance:**[View](#)