

220mm x 160mm x 12mm Metric Lab Jack



Stock **#62-009** **3 In Stock**

C\$1,666⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$1,666.00 each
Need More?	Request Quote

Product Downloads

General

Type:
Metric

Physical & Mechanical Properties

Type of Movement:
Linear (Z)

Guide System:
Pantograph

Stage Size (mm):
220 x 160

Construction:

Aluminum, Brass, & Stainless

70 **Height Adjustment (mm):**

1 **Leadscrew Pitch (mm):**

30 **Load Capacity (kg):**

170 **Maximum Height (mm):**

100 **Minimum Height (mm):**

6.3 **Weight (kg):**

0.1 (typical) **Parallelism (mm):**

Hardware & Interface Connectivity

Lead Screw **Type of Drive:**

Threading & Mounting

Mounting Threads:

Top: (35) M4 x 0.7

Bottom: (4) M6 x 1 on 200 x 140mm, (4) 4.5mm thru on 100mm Sq., (4) 4.5mm thru on 50mm Sq.

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 247:**

Product Details

- Rugged, Black Anodized Aluminum Construction
- Fine Lead Screw for Precision Movement
- Large Adjustment Knob for Maximum Control
- Locking Knob to Secure Vertical Positioning

Metric Labs Jacks feature a rugged construction and a fine screw movement that allows for precision adjustment of vertical positioning of most optical components or equipment, with a maximum weight capacity of up to 55 lbs. Top surfaces are precision finished mounting platforms with 1/4-20 and M4 tapped holes (see diagram). The bottom platforms have several additional M6 metric and 1/4-20 English sized clearance holes, which are spaced to adapt to common mounting surfaces. Metric Lab Jacks utilize a locking knob to fix vertical position at desired height. Each full revolution of the adjustment knob moves the platform vertically by 1mm.

These metric lab jacks offer stable, height-adjustable platforms ideal for laboratory and optical systems requiring manual vertical positioning. Designed for durability and repeatability, each lab jack integrates smoothly with breadboards, post assemblies, and manual translation stages. Their compact footprint and metric compatibility make them well-suited for modular lab setups where vertical lift precision and load stability are essential.

160 x 100mm Lab Jack ([#54-687](#)) and 132 x 80mm Lab Jack ([#56-336](#)) are compatible with the following stages: [#55-032](#), [#55-459](#), [#55-527](#), [#55-840](#), and [#55-841](#).

Note: Mount Lab Jacks on Metric or English Breadboards using [#12-796](#) to mount [#56-336](#) and [#54-687](#), and use [#12-797](#) to mount [#62-009](#).

Technical Information

