

TECHSPEC[®] 20mm Square Protected Silver Coated, λ/10 Mirror



Stock #68-328 [CONTACT US](#)

-

1

+

C\$144.20

ADD TO CART

Qty 1-5

C\$144.20

Qty 6+

C\$115.50

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate:
[Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 20.0 x 20.0
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 3.00 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 20.00
Width (mm): 20.00
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant