

TECHSPEC® 20mm VIS, Lateral Displacement Non-Polarized Beamsplitter



Lateral Displacement Beamsplitters

Stock **#47-189** **20+ In Stock**

⊖ 1 ⊕ C\$1,120.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$1,120.00 each
Qty 6-25	C\$889.00 each
Qty 26-99	C\$826.00 each
Need More?	Request Quote

Product Downloads

General

Non-Polarizing Beamsplitter **Type:**

Non-Polarizing **Type of Optics:**

Physical & Mechanical Properties

80.00 **Clear Aperture (%):**


Prism	Construction:
±0.1	Dimensional Tolerance (mm):
<2	Parallelism (arcmin):
Optical Properties	
±5	Angle Tolerance (arcsec):
20.00	Beam Separation (mm):
$R_{avg} < 0.5\% @ 430 - 670nm$	Coating Specification:
$ T_p - T_s < 6\%$	Extinction Ratio:
45.00	P-Polarization Transmission (%):
±10	Reflection/Transmission Tolerance (%):
45.00	S-Polarization Reflection (%):
N-BK7	Substrate: <input type="checkbox"/>
λ/8	Surface Flatness (P-V):
40-20	Surface Quality:
430 - 670	Wavelength Range (nm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Visible and NIR Coating Options Offered
- Simplifies Benchtop Layout
- Split Incident Beam into Two Displaced Parallel Beams

TECHSPEC® Lateral Displacement Beamsplitters output two parallel beams separated by a fixed distance. The beamsplitters consist of a precision [rhomboid prism](#) cemented to a [λ/8 right angle prism](#). The high tolerance design ensures the exiting beams are parallel to within 2 arcmin. TECHSPEC® Lateral Displacement Beamsplitters' entrance and exit faces feature a multi-layer anti-reflection (AR) coating for increased efficiency. Polarizing and non-polarizing coatings are available for these beamsplitters.

Technical Information



Size (A)	10mm	20mm
Beam Separation	10mm	20mm

