

[See all 17 Products in Family](#)

# 20mW, 30° Gaussian Line, Harsh Environment Green Diode



Stock **#64-828** 2 In Stock

-

 1 

+

 C\$1,330<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$1,330.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads



| General |                                           |
|---------|-------------------------------------------|
| 3B      | Laser Class - IEC:                        |
| >10,000 | Mean Time To Failures MTTF @ 25° (hours): |
| Diode   | Type of Laser:                            |

|                                    |                             |                     |
|------------------------------------|-----------------------------|---------------------|
| IIIb                               |                             | Laser Class - CDRH: |
| Physical & Mechanical Properties   |                             |                     |
| 20 Dia. x136 L                     | Dimensions (mm):            |                     |
|                                    |                             |                     |
| 87.00                              | Weight (g):                 |                     |
|                                    |                             |                     |
| 136.00                             | Housing Length (mm):        |                     |
|                                    |                             |                     |
| 20.00                              | Housing Diameter (mm):      |                     |
|                                    |                             |                     |
| Optical Properties                 |                             |                     |
| 532.00                             | Wavelength (nm):            |                     |
|                                    |                             |                     |
| 5.00                               | Beam Diameter (mm):         |                     |
|                                    |                             |                     |
| <1 without Line Optics             | Beam Divergence (mrad):     |                     |
|                                    |                             |                     |
| Green                              | Color:                      |                     |
|                                    |                             |                     |
| 30.00                              | Fan Angle (°):              |                     |
|                                    |                             |                     |
| 200mm to Collimation               | Focus Range (mm):           |                     |
|                                    |                             |                     |
| Electrical                         |                             |                     |
| 20                                 | Output Power (mW):          |                     |
|                                    |                             |                     |
| ±5%                                | Power Stability (%):        |                     |
|                                    |                             |                     |
| Hardware & Interface Connectivity  |                             |                     |
| Free Space                         | Output Type:                |                     |
|                                    |                             |                     |
| 4 Pins, M12                        | Connector:                  |                     |
|                                    |                             |                     |
| 5 - 30 DC                          | Input Voltage (V):          |                     |
|                                    |                             |                     |
| Environmental & Durability Factors |                             |                     |
| 0 to +35                           | Operating Temperature (°C): |                     |
|                                    |                             |                     |
| -10 to +80                         | Storage Temperature (°C):   |                     |
|                                    |                             |                     |
| Regulatory Compliance              |                             |                     |
| View                               | Certificate of Conformance: |                     |
|                                    |                             |                     |

## Product Details

- IP67 Rated Environmentally Sealed with Simple Thread Mount
- Electrically Isolated Housing
- Focusable with Gaussian and Uniform Line Options
- 5-30VDC Operation with Reverse Polarity Protection

Z-Laser Green Focusable Diode Modules are a high end, versatile green laser allowing wide voltage operation range with protection against surges, spikes and over voltage. This laser is available with Gaussian or Uniform line optics and is also available with simple spot output. Focusing can be achieved via the external focus mechanism, which does not interfere with the beam output. Z-Laser Green Focusable Diode Modules' electrical connections are made via an M12 connection with mounting available via an M18 threading. Application areas for these modules include machine vision, various materials processing, medical science and the automotive industry. [Mounting Accessories](#) and [Power Supply](#) also available.