

[See all 12 Products in Family](#)

## 20X T1.1 Mitutoyo LCD Plan Apo NIR Infinity Corrected Objective

See More by [Mitutoyo](#)



Stock **#37-550** 1 In Stock

-

1

+

C\$5,208<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$5,208.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                                        |               |
|----------------------------------------------------------------|---------------|
| 378-827-16                                                     | Model Number: |
| Compatible Tube Lens Focal Length (mm):<br>Focal Length: 200mm |               |
| Microscope Objective                                           | Type:         |
| Infinity Corrected                                             | Style:        |


|                                                 |  |                                                                                                                                                                                  |
|-------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Manufacturer:                                   |  | Mitutoyo                                                                                                                                                                         |
| Note:                                           |  | 1.1mm thick LCD cover-glass<br>Example Application: High magnification inspection through liquid crystal glass (LCD) or cutting and trimming of semiconductor wafer and circuits |
| Physical & Mechanical Properties                |  |                                                                                                                                                                                  |
| Length excluding Threads (mm):                  |  | 75.00                                                                                                                                                                            |
| Maximum Diameter (mm):                          |  | 34                                                                                                                                                                               |
| Weight (g):                                     |  | 305.00                                                                                                                                                                           |
| Optical Properties                              |  |                                                                                                                                                                                  |
| Compatible Cover Glass Thickness (mm):          |  | 1.1                                                                                                                                                                              |
| Design Wavelength DWL (nm):                     |  | 532, 1064                                                                                                                                                                        |
| Horizontal Field of View, 1/2" Sensor:          |  | 0.32mm                                                                                                                                                                           |
| Horizontal Field of View, 2/3" Sensor:          |  | 0.44mm                                                                                                                                                                           |
| Focal Length FL (mm):                           |  | 10.00                                                                                                                                                                            |
| Magnification:                                  |  | 20X                                                                                                                                                                              |
| Numerical Aperture NA:                          |  | 0.40                                                                                                                                                                             |
| Resolving Power (μm):                           |  | 0.7                                                                                                                                                                              |
| Depth of Field (μm):                            |  | 1.70                                                                                                                                                                             |
| Field of View, 24 Diameter Field Eyepiece (mm): |  | 1.2                                                                                                                                                                              |
| Field of View, 18 Diameter Field Eyepiece (mm): |  | 0.9                                                                                                                                                                              |
| Working Distance (mm):                          |  | 19.98                                                                                                                                                                            |
| Wavelength Range (nm):                          |  | 480 - 1800                                                                                                                                                                       |
| Parfocal Length (mm):                           |  | 95.37                                                                                                                                                                            |
| Immersion Liquid:                               |  | N/A                                                                                                                                                                              |
| Sensor                                          |  |                                                                                                                                                                                  |
| Maximum Sensor Format:                          |  | 2/3"                                                                                                                                                                             |
| Threading & Mounting                            |  |                                                                                                                                                                                  |
| Mounting Threads:                               |  | M26 x36 TPI                                                                                                                                                                      |
| Environmental & Durability Factors              |  |                                                                                                                                                                                  |
| Operating Temperature (°C):                     |  | -5 to +45                                                                                                                                                                        |
| Operating Humidity:                             |  | 20 - 80%                                                                                                                                                                         |
| Performance Assurance Temperature (°C):         |  | 23 ±2                                                                                                                                                                            |
| Regulatory Compliance                           |  |                                                                                                                                                                                  |
| RoHS 2015:                                      |  | <a href="#">Exempt</a>                                                                                                                                                           |
| Certificate of Conformance:                     |  | <a href="#">View</a>                                                                                                                                                             |
| REACH 241:                                      |  | <a href="#">Contains SVHC(s)</a>                                                                                                                                                 |

## Product Details

- Ideal for Brightfield Imaging and Laser-Based Applications through LCD Glass
- Excellent Performance at Nd:YAG Laser Lines
- Compensate for Cover-Glass Thickness of 0.7mm or 1.1mm

Mtutoyo NIR, NUV, and UV LCD Infinity Corrected Objectives combine the benefits of the standard MPlan Apo and MPlan Apo SL series objectives with enhanced spectral ranges. The NIR objectives are corrected from 480 to 1800nm, making them ideal for semiconductor and telecommunication inspection, or for laser cutting with common Nd:YAG lasers. The HR series offers an increased numerical aperture, providing smaller spot sizes and higher resolution. Mtutoyo NIR, NUV, and UV LCD Infinity Corrected Objectives compensate for common LCD glass thicknesses. The NUV and UV series of objectives have excellent performance at the second, third, and fourth Nd:YAG harmonics of 532nm, 355nm, and 266nm respectively.

Technical Information



| Dimensions   |        |        |        |           |
|--------------|--------|--------|--------|-----------|
| M Plan NIR   | A (mm) | B (mm) | C (mm) | W.D. (mm) |
| 20X, T0.7    | 75.00  | 34     | 32.2   | 20.0      |
| 20X, T1.1    | 75.02  | 34     | 32.2   | 19.98     |
| 50X, T0.7    | 78.04  | 34     | 32.2   | 17.26     |
| 50X, T0.7 HR | 77.74  | 34     | 32.2   | 9.60      |
| 50X, T1.1    | 77.87  | 34     | 32.2   | 17.13     |
| 100X         | 82.94  | 34     | 32.2   | 12.06     |
| HR 100X      | 85.13  | 39     | 37     | 9.87      |
| M Plan NUV   | A (mm) | B (mm) | C (mm) | W.D. (mm) |
| 20X, T0.7    | 78     | 34     | 32.2   | 16.96     |
| 50X, T0.7    | 80     | 34     | 32.2   | 14.76     |
| 100X, T1.1   | 83.97  | 34     | 32.2   | 11.03     |
| M Plan UV    | A (mm) | B (mm) | C (mm) | W.D. (mm) |
| 20X, T0.7    | 80     | 34     | 32.2   | 14.98     |
| 50X, T0.7    | 83     | 34     | 32.2   | 12.38     |