

2.3" x 2.3", 1.3" FL, Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#32-589** ☐ In Stock



1



C\$50.40

ADD TO CART

Qty 1-10

C\$50.40

Qty 11+

C\$43.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

33.02

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 2.3 x2.3
Dimensions (mm): 58.42 x58.42
Effective Diameter (inches): 2.0
Effective Focal Length EFL (inches): 1.30
Groove Density (grooves/inch): 125.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View