

TECHSPEC® 25.4mm Dia. 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#38-893** ☒ In Stock



1



C\$232.40

ADD TO CART

Qty 1-5

C\$232.40

Qty 6+

C\$205.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

90
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} ≥99.8% @ 532nm
Wavelength Range (nm): 523 - 537
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (532nm)
Design Wavelength DWL (nm): 532
Diameter (mm): 25.40 +0.00/-0.10
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View