


TECHSPEC® 25.0mm Dia. x -75 FL, VIS-NIR, UV Plano-Concave Lens



UV Fused Silica Plano-Concave (PCV) Lenses



Stock **#21-055** ☐ In Stock

☐ [Other Coating Options](#)

1

C\$208.60

ADD TO CART

Qty 1-5

C\$208.60

Qty 6+

C\$166.95

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-75.00
Substrate: Fused Silica (Corning 7980)
f#: 3.00
Numerical Aperture NA: 0.17
Coating: VIS-NIR (400-1000nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): -76.71
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 24
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Edge Thickness ET (mm): 4.74
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Note: Max. Flat Annulus is 0.3mm
Radius R₁ (mm): -34.38
Surface Quality: 40-20
Damage Threshold, Reference: View 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant