

TECHSPEC® 25.0mm Dia. x 500.0mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock **#47-387** ☐ In Stock
[Other Coating Options](#)

1 **C\$66.50**

ADD TO CART

Qty 1-9
C\$66.50
Qty 10+
C\$59.85
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
500.00 @587.6nm

Back Focal Length BFL (mm): 497.89
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.20 ±0.10
Edge Thickness ET (mm): 2.90
Radius R₁ (mm): 258.40
Clear Aperture CA (mm): 24
f#: 20.00
Numerical Aperture NA: 0.03
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant