

TECHSPEC<sup>®</sup> 25.0mm Diameter x 300.0mm FL, 980nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses

Stock **#69-575** CLEARANCE **6 In Stock**

☐ [Other Coating Options](#)

-

1

+

C\$36<sup>40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | C\$36.40 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                           |
|----------------------------------|---------------------------|
| Plano-Convex Lens                | Type:                     |
| Physical & Mechanical Properties |                           |
| 25.00 +0.0/-0.025                | Diameter (mm):            |
| <1                               | Centering (arcmin):       |
| 3.00 ±0.10                       | Center Thickness CT (mm): |

|                      |                         |
|----------------------|-------------------------|
| 2.50                 | Edge Thickness ET (mm): |
| 24                   | Clear Aperture CA (mm): |
| Protective as needed | Bevel:                  |

Optical Properties

|                                   |                                                       |
|-----------------------------------|-------------------------------------------------------|
| 300.00 @ 587.6nm                  | Effective Focal Length EFL (mm):                      |
| 298.02                            | Back Focal Length BFL (mm):                           |
| Laser V-Coat (980nm)              | Coating:                                              |
| R <sub>abs</sub> <0.25% @ 980nm   | Coating Specification:                                |
| N-BK7                             | Substrate: <input type="checkbox"/>                   |
| 40-20                             | Surface Quality:                                      |
| 1.5λ                              | Power (P-V) @ 632.8nm:                                |
| λ/4                               | Irregularity (P-V) @ 632.8nm:                         |
| ±1                                | Focal Length Tolerance (%):                           |
| 155.04                            | Radius R <sub>1</sub> (mm):                           |
| 12.00                             | f/#:                                                  |
| 0.04                              | Numerical Aperture NA:                                |
| 980                               | Design Wavelength DWL (nm):                           |
| 5 J/cm <sup>2</sup> @ 980nm, 10ns | Damage Threshold, By Design: <input type="checkbox"/> |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| Compliant | Reach 224:                  |
| View      | Certificate of Conformance: |

Product Details

- <0.25% Reflection at 980nm
- BBAR Coating Options Also Available: [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), [633nm](#), [785nm](#), 980nm, [1064nm](#), and [1550nm](#) V-Coated Options Offered

Our standard TECHSPEC® Plano-Convex lenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.>

LASER OPTICS

MADE BY EDMUND OPTICS®



Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
  - High-precision surface quality and flatness
  - Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts