

TECHSPEC® 25.4 x 25.4mm x -75mm FL, NIR I Laser Grade PCV Cylinder Lens



TECHSPEC Beam Shaping Fused Silica Cylinder Lenses

Stock **#36-129** ☐ In Stock

-

1

+

C\$252.00

ADD TO CART

Qty 1-5

C\$252.00

Qty 6+

C\$201.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
-75.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

f/#:
3.00

Numerical Aperture NA: 0.17
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): -77.06
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 5.31
Radius R₁ (mm): 34.38
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <3
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant