

TECHSPEC®

25.4 x 27.2mm EFL 30° Protected Aluminum 100Å Off-Axis Parabolic Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#35-514** ☒ In Stock

[Other Coating Options](#)

-

1

+

C\$427.00

ADD TO CART

Qty 1-5

C\$427.00

Qty 6+

C\$384.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):
27.22

Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 50.80
Coating : Protected Aluminum (400-2000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥85% @ 400 - 700nm R _{avg} ≥97% @ 2,000 - 12,000nm
Off-Set Angle (°) : 30
Parent Focal Length PFL (mm) : 25.4
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 400 - 2000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #47-111
Substrate : Aluminum 6061-T6
Y Offset (mm) : 13.61
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant