

TECHSPEC® 25.4 x 50.8mm EFL 90° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock **#35-502** ☐ In Stock

[Other Coating Options](#)

1

C\$259.00

ADD TO CART

Qty 1-5
C\$259.00
Qty 6+
C\$233.10
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):
50.80

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 50.80
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 25.4
Surface Figure, RMS: λ/4
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 400 - 2000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 50.8
Reflected Wavefront, RMS: λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant