


[See all 3 Products in Family](#)

25.4mm Dia., 1mm Thick, 3-5µm BBAR Coated, ISP Optics Silicon (Si) Window | HDAR35-SI-W-25-1

See More by [ISP Optics](#)



Stock #24-638 CLEARANCE **12 In Stock**

⊖ 1 ⊕ C\$155⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$155.40 each
Need More?	Request Quote

Product Downloads

General

HDAR35-SI-W-25-1 **Model Number:**

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

21.59	Clear Aperture CA (mm):
25.40 +0.00/-0.13	Diameter (mm):
1.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.27	Poisson's Ratio:
140	Young's Modulus (GPa):
1,150.00	Knoop Hardness (kg/mm²):

Optical Properties

BBAR (3000-5000nm)	Coating:
Silicon (Si)	Substrate: <input type="checkbox"/>
3.422 @ 5µm	Index of Refraction (n_d):
40-20	Surface Quality:
Coating Specification: R _{avg} < 0.5% @ 3 - 5µm R _{abs} < 1.5% @ 3 - 5µm	
3000 - 5000	Wavelength Range (nm):
2λ	Surface Flatness (P-V):

Material Properties

2.33	Density (g/cm³):
2.55	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- Transmission from 1.2 - 7µm
- Available Uncoated or HDAR Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications

ISP Optics Silicon (Si) Windows provide transmission in the Near-Infrared (NIR) and Mid-Wave Infrared (MMIR) from 1.2 - 7µm. Silicon features a Knoop Hardness of 1150, making it harder and less brittle than Germanium. A High-Durability Anti-Reflection (HDAR) coating option increases the durability of the substrate while significantly improving transmission from 3 - 5µm, enabling use in harsh environments. ISP Optics Silicon (Si) Windows are ideal for weight-sensitive IR applications due to its low density of 2.329 g/cm³, which is half as dense as Germanium and Zinc Selenide. These windows are ideal for NIR imaging applications and are important for detection of sources radiating at a black body temperature of 700K.