

25.4mm Dia., 700 - 1100nm, Positive Dispersion Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) Positive Dispersion Ultrafast Mirrors

Stock **#17-069** [CONTACT US](#)

- 1 +

C\$1,103.20

ADD TO CART

Qty 1-9
C\$1,103.20
Qty 10+
C\$995.40
Volume Pricing
Request Quote

Get Product Downloads	
Wedge (arcmin): 10	
Clear Aperture (%): 80	
Back Surface: Commercial Polish	

Coating Specification: R_{avg} >99.5% @ 700 - 1100nm (5° AOI, p-polarization)
GDD Specification: +100fs² @ 700 - 1100nm (5° AOI, p-polarization)
Wavelength Range (nm): 700 - 1100
Irregularity (P-V) @ 632.8nm: λ/10
Coating Type: Dielectric
Coating: Positive Dispersion (700-1100nm)
Diameter (mm): 25.40 +0.00/-0.05
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 5
Substrate: ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant