


25.4mm Dia., 3mm Thick, ISP Optics CaF₂ Infrared (IR) Diffuser | DIF-IR-25-3



IR Calcium Fluoride (CaF₂) Diffusers

Stock #16-819 17 In Stock

-

1

+

C\$315⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	C\$315.00 each
Qty 11+	C\$282.80 each
Need More?	Request Quote

Product Downloads

General	
DIF-IR-25-3	Model Number:
IR Diffuser	Type:
Note: Fine Grind first surface with a roughness (Ra) of □0.75 microns	
Physical & Mechanical Properties	


25.40 +0.00/-0.13	Diameter (mm):
Ground	Edges:
3.00 ±0.13	Thickness (mm):
Optical Properties	
Uncoated	Coating:
Calcium Fluoride (CaF ₂)	Substrate: ☐
300 - 8000	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Evenly Ground First Surface for Even Diffusion
- Low Index of Refraction Maximizes Throughput
- Broad Transmission Range

IR Diffusers feature an evenly fine ground first surface to produce even diffusion in the visible (VIS) and infrared (IR) spectra. Available in both ZnSe and CaF2 options with transmission ranges of 600nm-12000nm and 300nm-7000nm respectively, these diffusers can be used with a variety of coherent and incoherent light sources. The low index of refraction of calcium fluoride maximizes the throughput of these diffusers without use of an antireflection (AR) coating. IR Diffusers are ideal for use in laser calibration systems and general diffusion of VIS - IR light sources.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools