


25.4mm Dia. 488nm 45°, Low Cost Laser Line Mirror



Stock **#39-989** ☐ In Stock

-

1

+

C\$165.20

ADD TO CART

Qty 1-10
C\$165.20
Qty 11+
C\$147.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
20-10

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

90
Durability: ML-C-675C
Back Surface: Commercial Polish
Reflection at DWL (%): 99
Coating Specification: R _{abs} >99% @488nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (488nm)
Design Wavelength DWL (nm): 488
Diameter (mm): 25.40 +0.0/-0.1
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 45
Substrate: ☐ N-BK7

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View