

25.4mm Dia., 532nm,  $\lambda/4$  High Energy Waveplate



High Energy Quartz Waveplates

Stock **#39-170** **1 In Stock**

-

1

+

C\$917<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | C\$917.00 each                |
| Qty 11+        | C\$854.00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

High Energy Waveplate

Type:

Physical & Mechanical Properties

18.0

Clear Aperture CA (mm):

25.40

Diameter (mm):

Dimensional Tolerance (mm):

|                                                                         |  |
|-------------------------------------------------------------------------|--|
| +0/-0.2                                                                 |  |
| <div>Construction:<br/>Optically Bonded on UVFS (C7980) Substrate</div> |  |
| Parallelism (arcsec):                                                   |  |
| <3                                                                      |  |
| Optical Properties                                                      |  |
| Coating:                                                                |  |
| R <sub>avg</sub> <0.2%                                                  |  |
| Design Wavelength DWL (nm):                                             |  |
| 532                                                                     |  |
| Substrate: <input type="checkbox"/>                                     |  |
| Crystalline Quartz                                                      |  |
| Retardance:                                                             |  |
| λ/4                                                                     |  |
| Surface Quality:                                                        |  |
| 20-10                                                                   |  |
| Transmitted Wavefront, P-V:                                             |  |
| <λ/10 @ 632.8nm                                                         |  |
| Retardance Tolerance:                                                   |  |
| λ/250 @ 20°C                                                            |  |
| Damage Threshold, By Design: <input type="checkbox"/>                   |  |
| >20 J/cm <sup>2</sup> @ 1064nm, 10ns, 10Hz                              |  |
| Retardance Order:                                                       |  |
| 2nd                                                                     |  |

|                       |  |
|-----------------------|--|
| Threading & Mounting  |  |
| Mount Thickness (mm): |  |
| 6 ±0.2                |  |

|                             |  |
|-----------------------------|--|
| Regulatory Compliance       |  |
| RoHS 2015:                  |  |
| <a href="#">Compliant</a>   |  |
| Certificate of Conformance: |  |
| <a href="#">View</a>        |  |
| Reach 247:                  |  |
| <a href="#">Compliant</a>   |  |

## Product Details

- Damage Threshold up to >20 J/cm<sup>2</sup> @ 1064nm
- λ/4 and λ/2 Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both λ/4 and λ/2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm<sup>2</sup> at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.