

25.4mm Dia, 650 - 1100nm, $\lambda/4$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-044** ☐ In Stock



1



C\$1,372.00

ADD TO CART

Qty 1-5
C\$1,372.00
Qty 6+
C\$1,197.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
>20.0

Coating:
R_{avg} <0.75% @ 650 - 1100nm

Diameter (mm):
25.40

Substrate: ☐

Crystal Quartz and MgF ₂
Retardance: λ/4
Surface Quality: 40-20
Thickness (mm): 6.00 ±0.2
Type: Achromatic Waveplate
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/4 @ 632nm
Parallelism (arcsec): <10
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: λ/100 @ 20°C
Coating Specification: R _{avg} <0.75% @ 650 - 1100nm
Wavelength Range (nm): 650 - 1100
Damage Threshold, By Design: ☐ >5 J/cm ² @ 1064nm, 10ns, 10Hz
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant