

TECHSPEC®

25.4mm Dia. x 100mm FL, 8-12µm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-551** ☐ In Stock

☐ [Other Coating Options](#)

-

1

+

C\$539.00

ADD TO CART

Qty 1-10

C\$539.00

Qty 11+

C\$485.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
100.00 @ 10.6µm

Back Focal Length BFL (mm): 98.96
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} ≤0.5% @ 8 - 12μm
Substrate:  Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: λ10
Irregularity (P-V) @ 10.6μm: λ20
Centering, ETD (μm): ≤12.7
Center Thickness CT (mm): 2.50 ±0.10
Edge Thickness ET (mm): 1.92
Radius R₁ (mm): 140.27
Clear Aperture CA (mm): 22.86
f#: 3.94
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 8000 - 12000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View