

TECHSPEC® 25.4mm Dia. x 150mm FL, 355nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#38-675** ☐ In Stock

[Other Coating Options](#)

1 **C\$284.20**

ADD TO CART

Qty 1-5

C\$284.20

Qty 6+

C\$226.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.025

Effective Focal Length EFL (mm):
150.00 @ 355nm

Back Focal Length BFL (mm):
147.33

Coating: Laser V-Coat (355nm)
Coating Specification: R_{abs} <0.25% @ 355nm
Substrate: Fused Silica (Corning 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 2.77
Radius R₁ (mm): 71.41
Clear Aperture CA (mm): 21.59
f/#: 5.91
Numerical Aperture NA: 0.08
Design Wavelength DWL (nm): 355
Type: Plano-Convex Lens
Bevel: Protective Bevel As Needed
Damage Threshold, By Design: 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View