

[See all 5 Products in Family](#)

## 25.4mm Dia x 150mm FL, Uncoated Meniscus Lens



Stock **#72-432** **20+ In Stock**

- 1 + C\$39<sup>.20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	C\$39.20 each
Qty 10-24	C\$35.35 each
Qty 25-49	C\$31.50 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Meniscus Lens **Type:**

#### Physical & Mechanical Properties

25.40 +0.00/-0.10 **Diameter (mm):**

3.10 ±0.10 **Center Thickness CT (mm):**

Centering (arcmin):

<3

Clear Aperture CA (mm):

22.86

Edge Thickness ET (mm):

2.00

## Optical Properties

Effective Focal Length EFL (mm):

150.00 @ 587.6nm

Substrate:

[N-BK7](#)

f#:

5.91

Numerical Aperture NA:

0.08

Coating:

Uncoated

Back Focal Length BFL (mm):

146.34 @ 587.6nm

Design Wavelength DWL (nm):

587.6

Radius R<sub>1</sub> (mm):

43.36

Radius R<sub>2</sub> (mm):

95.998

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

3 Rings

Irregularity (P-V) @ 632.8nm:

0.5 Rings

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- Positive Meniscus Lens Designs
- Minimize Spherical Aberration and Reduce Spot Sizes
- 350 – 2,200nm Wavelength Range

Positive Meniscus Lenses are convex-concave lenses manufactured from N-BK7 optical glass and are designed to minimize spherical aberration and reduce spot sizes in focusing applications. When used to focus a collimated beam, the lenses should be oriented with the convex surface towards to light source to minimize spherical aberration. Combining a positive meniscus lens with another lens in a multi-element optical design will allow for a shortening of the focal length and an increase in the numerical aperture (NA) of a system without introducing significant spherical aberrations. Positive Meniscus Lenses are available with focal lengths ranging from 100 to 300mm in 25.4mm diameters sizes, allowing for easy integration into benchtop systems.