

TECHSPEC® 25.4mm Dia. x 75mm EFL, 355nm 0-45°, Concave Laser Line Mirror



Laser Line Concave Mirrors

Stock **#39-956** ☒ In Stock

-

1

+

C\$224.00

ADD TO CART

Qty 1-5

C\$224.00

Qty 6+

C\$201.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Design Wavelength DWL (nm):
355

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm): 25.40 +0.00/-0.20
Effective Focal Length EFL (mm): 75.00
Radius of Curvature (mm): 150.00
Coating: Laser Mirror (355nm)
Coating Specification: R_{abs} >99.80% @ 355nm (0-45° AOI)
Coating Type: Dielectric
Back Surface: Fine Grind
Center Thickness CT (mm): 5.81
Clear Aperture (%): 90
Edge Thickness ET (mm): 6.35 ±0.10
Radius R₁ (mm): 150.00
Type: Concave Mirror
Wavelength Range (nm): 351 - 358
Irregularity (P-V) @ 632.8nm: λ/10
Damage Threshold, Reference: 1 MW/cm² @ 355nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View