

TECHSPEC® 25.4mm Dia. x 88.9mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#49-769** ☐ In Stock

☐ [Other Coating Options](#)

1

C\$147.00

ADD TO CART

Qty 1-5

C\$147.00

Qty 6+

C\$117.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

88.90
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 83.96
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.40
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.00 ±0.20
Center Thickness CT 1 (mm) : 6.00 ±0.10
Center Thickness CT 2 (mm) : 4.00 ±0.10
Radius R₁ (mm) : 56.98
Radius R₂ (mm) : -40.06
Radius R₃ (mm) : -162.82
Edge Thickness ET (mm) : 8.07
Substrate: ☐ N-BAK1 / N-SF8
Surface Quality : 40-20
f/#: 3.5
Numerical Aperture NA : 0.14
Coating : MgF ₂ (400-700nm)
Coating Specification : R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View