


25.4mm Diameter, 3.2mm Through Hole, Sapphire Window



25.4mm Diameter, 3.2mm Through Hole, Sapphire Window

Stock #17-215 ☐ In Stock



1



C\$147.00

ADD TO CART

Qty 1-5

C\$147.00

Qty 6+

C\$132.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence ($n_o - n_e$): 0.008 for Visible Light Orthogonal to Optical Axis
Diameter (mm): 25.40 ±0.127
Through Hole Diameter (mm): 3.20 ±0.127
Thickness (mm): 1.00 ±0.127
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8
Density (g/cm³): 3.97
Index of Refraction n_d: 1.77
Knoop Hardness (kg/mm²): 1900
Parallelism (arcmin): ≤3.5
Poisson's Ratio: 0.27
Substrate: Sapphire (Al ₂ O ₃)
Surface Flatness (P-V): 2λ (typical)
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 330 - 5500
Young's Modulus (GPa): 435

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant