



600-1000nm, 25.4mm Dia. x 75mm EFL, Ultrafast-Enhanced Silver Concave Laser Mirror



TECHSPEC® Ultrafast-Enhanced Silver Concave Laser Mirrors

Stock **#13-064** ☐ In Stock

-

1

+

C\$238.00

ADD TO CART

Qty 1-5

C\$238.00

Qty 6+

C\$210.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):
25.40 +0.00/-0.20

Effective Focal Length EFL (mm): 75.00
Radius of Curvature (mm): 150.00
Coating: Ultrafast-Enhanced Silver (600-1000nm)
Coating Specification: R_{avg} >99% @ 600 - 1000nm, 0° R_s >99% @ 540 - 1000nm, 45° R_p >98.5% @ 730 - 870nm, 45°
GDD Specification: 0 ±20fs² @ 600 - 1050nm
Coating Type: Ultrafast-Enhanced Silver
Clear Aperture (%): 80
Edge Thickness ET (mm): 6.35 ±0.10
Type: Concave Mirror
Wavelength Range (nm): 600 - 1000
Irregularity (P-V) @ 632.8nm: λ/10
Damage Threshold, Reference: 0.3 J/cm² @ 800nm, 48fs, 1 pulse (typical) 0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View